



# SCP Compact Pressure Sensors

Catalog MSG33-2379/US



ENGINEERING YOUR SUCCESS.

**Application**

The SCP pressure sensor belongs to the Parker family of accessories provided to complement electronic control systems. The SCP sensor family is a range of 0-5 V pressure transmitters for mobile hydraulic applications.

These transmitters are available in three standard pressure ranges; 35 bar (507 psi), 250 bar (3625 psi) and 500 bar (7250 psi). The sensors feature compact construction, high linearity and excellent electromagnetic interference resistance.

**Properties**

**Reliability**

The SCP has stainless steel construction for strength. The sensor cells use thin film technology with no internal o-rings or fluid. The high pressure capability makes the sensor very robust and able to withstand heavy vibrations.

**Electromagnetic immunity**

The design of the SCP separates the sensor electronics from the connector. This ensures a high level of EMI protection.

**Installation**

The interface type of the SCP is a SAE 6 (9/16"-18UNF) thread with o-ring seal. The connector is a sealed, Deutsch DT type and is integrated into the sensor body.

The sealed connector gives the sensor protection for exposed outdoor applications. The SCP is easy to install and remove, even in field conditions.

**General**

Weight	50 g
Operating temperature	-40 °C to 125 °C
Storage temperature	-40 °C to 125 °C
Pressure range	see code in table below
Over pressure	
code "035"	Max 70 bar
code "250"	Max 500 bar
code "500"	Max 1000 bar
Burst pressure	
code "035"	Min 140 bar
code "250"	Min 1000 bar
code "500"	Min 2000 bar

**Accuracy**

Total error (-40°C to 125°C)	Max 2.5 % FS
Total error ( -25°C to 100°C)	Max 1.5 % FS
Repeatability	Max 0.2 %

**Electrical specifications**

Output at FS <sup>1)</sup>	4.5 V (90%)
Zero output <sup>1)</sup>	0.5 V (10%)
Supply Voltage (Vs)	5.0 Vdc
Load resistor	Min 10 kΩ
Current supply	Max 6 mA
Response time	Max 1 msec

*1) The output is ratiometric (code "R") to supply voltage, Vs.*


**Threaded interface**

code "6"	SAE 6, 9/16"-18 UNF
----------	---------------------

**Connector**

Integral to sensor	see code in table below
--------------------	-------------------------

**Model code: Sensor, Compact Pressure, Type 05, Electronic Controls Division**



**Environmental protection**

**EMI**



EN 61000-6-2 (interference resistance)  
 EN 61000-6-3 (interference emissions)

**Mechanical environment**

IEC 60068-2-6 Fh (vibration)  
 IEC 60068-2-27 Es (shock)

**Climate environment**

EN/IEC 60529 (IP67)



units = mm

**Ordering part numbers<sup>2)</sup>**

Model code	Part number
SCP05-035-R6-0D-ECD	2820012
SCP05-500-R6-0D-ECD	2820013
SCP05-250-R6-0D-ECD	2820016

2) Other configurations possible, consult factory.



**WARNING - USER RESPONSIBILITY**

**FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.**

- This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.
- The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.
- To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

**OFFER OF SALE**

The items described in this document are hereby offered for sale by Parker-Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the detailed "Offer of Sale" available from your Parker representative or at [www.parker.com](http://www.parker.com).



**WARNING - California Proposition 65**

This product can expose you to chemicals including NICKEL COMPOUNDS which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

# Parker Motion Systems International Sales Offices

## North America

### Motion Systems Group

#### Headquarters

6035 Parkland Boulevard  
Cleveland, OH 44124-4141 USA  
Tel: 216-896-3000  
Fax: 216-896-4031

### Parker Canada Division

160 Chisholm Drive Milton  
Ontario Canada L9T 3G9  
Tel: 905-693-3000  
Fax: 905-876-1958

### Parker Hannifin de México

Industrial Hydraulic Sales  
Eje Uno Norte No.100  
Parque Industrial Toluca 2000  
Toluca, Edo, de Mexico CP 50100  
Tel: 52 722 275 4200  
Fax: 52 722 279 9308

### Parker Hannifin de México

Mobile Hydraulic Sales  
Via de FFCC a Matamoros 730  
Apodaca, NL, de Mexico CP 66600  
Tel: 52 81 8156 6000  
Fax: 52 81 8156 6068

## Europe

### Motion Systems Group

#### Headquarters

La Tuilière 6  
1163 Etoy - Switzerland  
Tel: 41 21 821 8500  
Fax: 41 21 821 8580

## South Africa

### Parker Hannifin Africa Pty Ltd

P.O. Box 1153  
ZA-Kempton Park 1620,  
Republic of South Africa  
Tel: 27 11 961 0700  
Fax: 27 11 392 7213

## Mobile Sales

### Mobile Sales Organization and Global Sales

850 Arthur Avenue  
Elk Grove Village, IL 60007 USA  
Tel: 847-258-6200  
Fax: 847-258-6299

## Industrial Sales

### Central Region

1042 Maple Avenue  
Unit 331  
Lisle, IL 60532 USA  
Tel: 630-964-0796

### Great Lakes Region

6035 Parkland Boulevard  
Cleveland, OH 44124-4141 USA  
Tel: 216-896-2740  
Fax: 866-498-7507

### Gulf Region

20002 Standing Cypress Drive  
Spring, TX 77379 USA  
Tel: 817-473-4431  
Fax: 888-227-9454

### Southwest Region

700 S. 4th Avenue  
Mansfield, TX 76063 USA  
Tel: 817-473-9341  
Fax: 817-473-2680

### Mid Atlantic and Southeast Regions

1225 Old Alpharetta Road  
Suite 290  
Alpharetta, GA 30005 USA  
Tel: 770-619-9767  
Fax: 770-619-9806

### Midwest Region

8145 Lewis Road  
Minneapolis, MN 55427 USA  
Tel: 763-513-3535  
Fax: 763-544-3418

### Northeast Region

P.O. Box 396  
Pine Brook, NJ 07058 USA  
Tel: 973-227-2565  
Fax: 973-227-2467

### Northwest Region

6458 North Basin Avenue  
Portland, OR 97217 USA  
Tel: 503-283-1020  
Fax: 866-611-7308

### Pacific Region

8460 Kass Drive  
Buena Park, CA 90621  
Tel: 714-228-2510  
Fax: 714-228-2511

## Asia Pacific

### Parker Hannifin Shanghai Ltd

280 Yunqiao Road,  
Jin Qiao Export Processing Zone  
Shanghai 201206, China  
Tel: 86 21 2899 5000  
Fax: 86 21 6445 9917

### Parker Hannifin Hong Kong Ltd

8/F, Kin Yip Plaza  
9 Cheung Yee Street  
Cheung Sha Wan, Hong Kong  
Tel: 852 2428 8008  
Fax: 852 2425 6896

### Parker Hannifin Korea Ltd

9F KAMCO Yangjae Tower  
949-3 Dogok1-dong, Gangnam-gu  
Seoul, 135-860, Korea  
Tel: 82 2 559 0400  
Fax: 82 2 556 8187

### Parker Hannifin India Pvt Ltd

Plot No. EL-26, MIDC  
TTC Industrial Area  
Mahape, Navi Mumbai, 400 709 India  
Tel: 91 22 6513 7081  
Fax: 91 22 2768 6841

### Parker Hannifin Australia

Parker Hannifin Pty Ltd.  
9 Carrington Road  
Castle Hill, NSW 2154, Australia  
Tel: 612 9634 7777  
Fax: 612 9842 5111

## Latin America

### Parker Hannifin Ind. e Com. Ltda Hydraulics Division

Av. FredericoRitter, 1100  
94930-000 Cachoeirinha RS, Brazil  
Tel: 55 51 3470 6090  
Fax: 55 51 3470 9281

### Parker Hannifin Argentina S.A.I.C.

Stephenson 2711  
1667-Tortuguitas-Malvinas Argentinas  
Pcia. de Buenos Aires, Argentina  
Tel: 54 3327 44 4129  
Fax: 54 3327 44 4199

### Pan American Division

7400 NW 19th Street, Suite A  
Miami, FL 33126 USA  
Tel: 305-470-8800  
Fax: 305-470-8808

